GENESIS HIGHSPEED



Isolated Digitizer 6600 Specifications

GEN SERIES ISOLATED DIGITIZER 6600

The Isolated Digitizer 6600 is used in the most demanding test lab applications requiring high voltage isolation and safe and accurate measurements in harsh electrical environments.

It is available in four different configurations. There are two mechanical variants, one for use in medium and one for use in high voltage environments. Each model is available with 25 MS/s or **100 MS/s** digitizing speed per channel.

The Medium Voltage version is single layer shielded and uses AC power with an

Analog input section

| # of channels 1 per transmitter, | | | | |
|---|--|--|--|--|
| | (4 per receiver board) | | | |
| Input type | single-ended to isolated | | | |
| | common (unbalanced | | | |
| | differential) | | | |
| Coupling | AC / DC / GND | | | |
| Connector | fully isolated BNC | | | |
| Ranges | ± 20 mV to ± 100 V | | | |
| - | Full Scale in 1, 2, 5 steps | | | |
| Offset | automatic, equal to span | | | |
| Impedance | 1 MΩ (± 2 %) // 38 pF (± 5 %) | | | |
| Bandwidth | 100 MS/s: 25 MHz @ –3 dB | | | |
| | 25 MS/s: 5 MHz @ −3 dB | | | |
| Risetime | 100 MS/s: 14 ns | | | |
| | 25 MS/s: 75 ns | | | |
| CMRR | 100 dB @ 80 Hz | | | |
| MSE | 0.1 % FS ± 50 μV RTI | | | |
| Offset error | | | | |
| Noise (RMS) | ± 0.05 % FS ± 0.1 mV RTI | | | |
| Overload | 250 V peak protected for $\geq \pm 2$ V | | | |
| | 125 V peak protected for < ± 2 V | | | |
| | 800 V peak transient (impulse | | | |
| | spark-over voltage at 1 kV/ms) | | | |
| Recovery time | *10 ns to 10 % accuracy | | | |
| | 30 ns to 1 % accuracy | | | |
| | 40 ns to 0.1 % accuracy | | | |
| Non-Linearity 0.05 % max | | | | |
| * after 200 % over | rload, 1 kHz, 1 V range, Wideband filter | | | |
| | | | | |

isolation voltage of 10 kV. This MV version can be used for isolated measurements up to 10 kV while being powered by AC power. In case AC power is lost, the MV version can securely finish the acquisition by running from internal battery for up to 5 minutes. When it is reconnected to AC power, the internal battery will be recharged. The High Voltage version is also single layer shielded and exclusively battery powered. The removable batteries run for a minimum of 24 hours, with a software controlled "sleep mode" that extends that time significantly.

Fiber optic link

| Light source Dyn. range Connectors Type Wavelength Cable length Correction | Class 1 laser product + 9 dB LC-type on receiver, SC-RJ on transmitter Multimode 50/125 µm 850 nm up to 800 m using a single cable; each patch panel connector will reduce length by 100 m automatic cable length correction to prevent cross channel skew |
|--|--|
| Acquisition | |
| | |

25 MS/s or 100 MS/s Sample rate per channel synchronous sampleing Sampling **AD-Resolution** 100 MS/s: 14-bit (0.006 %) 25 MS/s: 15-bit (0.003 %) 16-bit enhanced resolution for sample rates \leq 10 MS/s 6th order Bessel low pass **AA Filter** 100 MS/s: 10 MHz 25 MS/s: 5 MHz

Hot-swappable batteries allow for continuous operation: while charging one set, the unit operates on a spare set. Standard Lithium-Ion batteries are used to ensure proper operation in various environments.

A system always consists of one (or more) Isolated Digitizer transmitters and at least one (or more) receiver cards. One receiver card serves up to four transmitters. As these are calibrated independant from a receiver channel, they can easily be switched between receiver boards or even mainframes while maintaining their calibrated status.

Filtering

| Digital filters | 100 MS/s model: at 100 MS/s no filter; or else user-selectable from 5 MHz to 50 kHz in 12 steps 25 MS/s model: user-selectable from 5 MHz to 50 kHz in 12 steps | | | |
|--|--|--|--|--|
| Monitor output (receiver side) | | | | |
| # of outputs Output level DAC Filter Delay | one BNC per channel on receiver front panel ± 5 V FS uncalibrated 14-bit @ 100 MS/s 6-pole Bessel @ 10 MHz < 1 µs (WB) to 12 µs (50 kHz) | | | |
| Transient memory (receiver side) | | | | |

Standard 400 MegaSample memory per card, shared by enabled channels. 100 to 400 MS per channel Memory



Triggering

| | channel | has | а | dual-le | vel | trigger | |
|-------------------|---------|---|------|--------------------------------|------|---------|--|
| detect | • · · | | | | | | |
| Pre/post Rate | | o to full memory length every 10 ms, up to 100 | | | | | |
| | | triggers per second, zero re-arm time | | | | | |
| Resolu | ution | 16-bit (0.0015%), each level | | | | | |
| Acquisition modes | | | | | | | |
| | | | | | | | |
| Record | ler | for co | ntin | uous ad | quis | sition | |
| Scope | | for rep | peti | tive phe | enom | iena | |
| Transi | ent | | | nittent e | | , | |
| | | single | or | A-B-A ti | meb | ase | |
| Data s | storage | | | | | | |
| | | | | | | | |
| Record | ler | of cor | ntro | lirectly PC; un Iration. | | | |
| | | | | sfer rate | 2:5 | MS/ch. | |
| Scope | | | | ransient | - | | |
| Transi | ent | | | ransient | | | |
| | | single | or | A-B-A ti | meb | ase | |
| | | | | | | | |
| | | | | | | | |

••••

Isolated Digitizer 6600 Specifications

Ordering information and options

Physical and environmental specifications

Single channel transmitters

845-082100 High Voltage 100 MS/s 845-082200 High Voltage 25 MS/s Medium Voltage 100 MS/s 845-082300 845-082400 Medium Voltage 25 MS/s

Four channel receiver

Receiver card for GEN 845-079500 DAQ products. Accepts all Isolated Digitizer models. Includes 400 MS transient memory.

Notes

- HV versions include battery charger
- MV versions have AC power supply and built-in battery charger
- Receiver card accepts 1 to 4 transmitters
- Transmitter models may be mixed on a single receiver card. Sample rate is set to lowest available sample rate.

Connection cables (sold seperately)

Standard cables

IP20 connector on sender side 869-913100 10 meter cable pair, LC-SCRJ 869-9132 20 meter cable pair, LC-SCRJ 50 meter cable pair, LC-SCRJ 869-913300

Industrial grade cables


| IP67 connector | r on sender side |
|----------------|---------------------------|
| 869-913500 | 10 m cable pair, LC-SCRJ |
| 869-913600 | 20 m cable pair, LC-SCRJ |
| 869-913700 | 50 m cable pair, LC-SCRJ |
| 869-913800 | 100 m cable pair, LC-SCRJ |

| Dimensions (WxDxH) including handles, etc. | 175 x 265 x 119 mm (6.86 x 10.44 x 4.68 inch) | 175 x 280 x 119 mm (6.86 x 11.3 x 4.68 inch) |
|---|--|--|
| Weight (maximum) | 3 kg (6.6 lb) | 4 kg (8.8 lb) incl. batteries |
| Shielding | Single metal shielding in plastic housing | Single metal shielding in plastic housing ^(note 1) |
| Power supply | 115/230 VAC, 47-63 Hz, 12 VA or internal battery | Internal removable batteries |
| Isolation when AC powered | 10 kV | N/A |
| Operating temperature | 0 °C to +40 °C (+32 °F to +104 °F) | -15 °C to +50 °C ^(note 2) (+5 °F to +122 °F) |
| Battery | Internal, rechargeable, NiMH, 12 V @ 300 mAh; built-in charger | 2x Removable, rechargeable, Lithium-Ion, 11.1 V @ 6600 mAh; SmartBattery 1.1 compliant; external charger |
| Battery operation time | 5 minutes | 24 hours |
| Battery life time in 'sleep' | 30 minutes | 90 hours |
| Power switch | standby (charger active) | power on/off |
| LED indicator | 1 x mains/battery status | 2 x battery status |

Medium Voltage Models

Note 1: Correct operation has been verified by placing a front-end cabinet within 1 meter of an EMC field created by a 80 kA current. Note 2: Minimum temperature may be lower when fully loaded batteries are inserted @ 20 °C prior to performing a measurement.





You can use the Isolated Digitizers 6600 in a variety of applications with complete confidence.



The latest generation of the Isolated Digitizer outperforms previous version (shown left) with 1/2 of the size and 1/4 of the weight.

| C | |
|-----|--|
| IBM | |

www.hbm.com/highspeed

HBM Genesis HighSpeed products were previously sold under the Nicolet brand. The Nicolet brand is owned by Thermo Fisher Scientific Inc. Corporation.

High Voltage Models

HBM reserves the right to change this document without notice. It provides outline specification only and cannot be used as the basis of any contract.